

AR3100HACS

APC NetShelter SX, Server Rack Enclosure,
42U, Black, 1991H x 600W x 1070D mm



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Number of rack unit	42U
Provided equipment	Casters Doors Ground studs Installation guide Leveling feet Mounting Hardware Roof Side Panels

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	23.62 in (60 cm)
Depth	42.13 in (107 cm)
Net Weight	275.78 lb(US) (125.09 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Net Depth with Stabilizing Feet	42.13 in (1070.10 mm)
Maximum Mounting Depth	35.79 in (90.91 cm)
Minimum Mounting Depth	7.40 in (18.8 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 14 gauge post 18 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	2250 Lb(US) (1020.58 kg) dynamic 3750 lb(US) (1700.97 kg) static

Conformance

Standards	EIA-310D
-----------	----------

Ordering and shipping details

GTIN	731304241553
Package weight(Lbs)	318.68 lb(US) (144.55 kg)

Packing Units

Package 1 Height	83.39 in (211.8 cm)
Package 1 width	35.39 in (89.9 cm)
Package 1 Length	47.99 in (121.9 cm)
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------