



Overview

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

Main

Main Input Voltage	208 V 3 phase 3 phase 3 phase
Main Output Voltage	208 V 208 V 3 phase 415 V 3 phase 480 V 3 phase 600 V 3 phase
Provided Equipment	Installation guide

Physical

Color	Black
Height	78.90 in (200.4 cm)
Width	11.81 in (30 cm)
Depth	42.13 in (107 cm)
Net Weight	295.42 lb(US) (134 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	60 Hz
Number of input connectors	1 Hard Wire 5-wire (3PH + N + G)
Input current limits	200 A

Output

Maximum Total Current Draw per Phase	200 A
--------------------------------------	-------

Conformance

Standards	UL 60950-1
-----------	------------

Environmental

Ambient Air Temperature for Operation	23...104 °F (-5...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...10000 ft (0.00...3048.00 m)

Ordering and shipping details

GTIN	731304296256
Package weight(Lbs)	341.72 lb(US) (155 kg)

Packing Units

Package 1 Height	84.65 in (215 cm)
Package 1 width	33.39 in (84.8 cm)
Package 1 Length	47.64 in (121 cm)
SCC14	10731304296253

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------