

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Product	Switching device
Line Rated Current	200 A
Certifications	UL listed
Disconnect Type	Non-fusible disconnect switch
Mounting Type	Surface
Number of Poles	3
Wire Size	AWG 6...300 kcmil (copper or aluminium)

Complementary

Width	23.88 in
Height	30.88 in
Depth	11.75 in
Tightening torque	340 lbf.in (AWG 6...300 kcmil)

Ordering and shipping details

Category	00033 - DT SWITCH,NEMA1
Discount Schedule	DE1
GTIN	00785901017653
Nbr. of units in pkg.	1
Package weight(Lbs)	63
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------