

Product data sheet

Specifications



NEMA combination starter, Type S, 30A fusible disconnect, Size 1, 27A, Motor Logic SSOLR, 120VAC coil, NEMA 3R/12 [TAA]

8538SCASP6

Product availability: Stock - Normally stocked in distribution facility

Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Line Rated Current	27 A
Number of Poles	3P
Horsepower Rating	10 hp 460 V AC, 3 phase 10 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on LED Green indicator off LED
Auxiliary Contacts	2 NO + 2 NC
Thermal overload type	Solid state Motor Logic class 10/20 6...18 A
Disconnect Type	Fusible disconnect switch H and K, 30 A, electrical SPDT
NEMA size	1
Height	24 in (609.6 mm)
Depth	8.34 in (211.84 mm)
Width	9.5 in (241.3 mm)

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
Product Certifications	CSA UL Listed

Ordering and shipping details

Category	US10CP121213
Discount Schedule	0CP1
GTIN	785901875543

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	10.80 in (27.432 cm)
Package 1 Width	13.10 in (33.274 cm)
Package 1 Length	29.10 in (73.914 cm)
Package weight(Lbs)	38.940 lb(US) (17.663 kg)

Compliance

Compliance	TAA
------------	-----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Not compliant
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Take-back	No