

8501XDO80XDLV62

NEMA Control Relay, Type X, latching, 10A resistive at 600 VAC, 8 normally open contacts, 115/125 VDC coil



Main

Range	8501X
Relay Type	Latching
Product	Relay
Current Rating	10 A AC 5 A DC
Contact Configuration	8 NO 8 standard contact cartridges
Number of Poles	8P
Coil Voltage	115/125 V DC
Voltage Rating	250 V DC
Mounting Type	Panel
Operating Temperature	-40...160 °F (-40...71 °C)
Electrical Connection	Screw clamp terminals
Certifications	CSA UL Listed CE
Operating Time	37 ms - pick-up 45 ms - drop-out
Height	3.56 in (90.42 mm)
Width	2.23 in (56.64 mm)
Depth	8.96 in (227.58 mm)

Ordering and shipping details

Category	21157-8501 XDO (DC)
Discount Schedule	CP2
GTIN	785901018155
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.00 lb(US) (1.814 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------