

Product data sheet

Specifications

SQUARE D



Power distribution block, Linergy, 2 pole, 1 line, 6 load, 335A Cu, 270A Al, 600V

9080LBA263106

Product availability: Stock - Normally stocked in distribution facility

Main

Range	9080LB
Product	Power Distribution Block
Current Rating	335 A copper 270 A aluminium
Short Circuit Current Rating	65 kA

Complementary

Voltage Rating	600 V AC/DC
Mounting Type	Surface mount
Number of poles	2
Terminals per Pole	1 line 6 load
Wire Size	Line 1, AWG 6...400 kcmil, copper or aluminium Load 6, AWG 14...AWG 2, copper or aluminium
Electrical Connection	Tin plated aluminium lugs
SCCR	65 kA UL 508 A
Ambient Air Temperature for Operation	-40...150 °C (-40...302 °F)
Block Material	Phenolic: block
Terminal Tightening Torque	Load lug 45 lbf.in (5.08 N.m) AWG 6...AWG 4 copper or aluminium Load lug 40 lbf.in (4.5 N.m) AWG 8 copper or aluminium Load lug 35 lbf.in (4.0 N.m) AWG 14 copper Load lug 50 lbf.in (5.6 N.m) AWG 2 copper or aluminium Load lug 35 lbf.in (4.0 N.m) AWG 12...AWG10 copper or aluminium Line lug 375 lbf.in (42.4 N.m) AWG 6...400 kcmil copper or aluminium
Wire stripping length	Line: 1.06 in (26.92 mm) Load: 0.56 in (14.22 mm) for top connection Load: 1 in (25.4 mm) for bottom connection
Height	4.75 in (120.65 mm)
Width	4.16 in (105.66 mm)
Depth	2.91 in (73.91 mm)
End Barrier	9080LB32

Environment

Certifications	CSA file 70361 class 6228 01 UL recognized E60616 CCN XCFR2 CE
----------------	--

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	US10CP121711
Discount Schedule	0CP1
GTIN	785901157007
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	3.10 in (7.874 cm)
Package 1 Width	4.40 in (11.176 cm)
Package 1 Length	5.40 in (13.716 cm)
Package weight(Lbs)	18.240 oz (517.095 g)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Technical Illustration

Dimensions

