



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	200 V 208 V 230 V
Main Output Voltage	208 V 230 V
Input Connection Type	IEC 60320 C20
Number of rack unit	1U
Cable length	8.2 ft (2.50 m)
Provided Equipment	Cord retention bracket(s) Installation guide Rack Mounting brackets User Manual

Physical

Height	1.73 in (4.4 cm)
Width	17.48 in (44.4 cm)
Depth	4.02 in (10.2 cm)
Net Weight	3.84 lb(US) (1.74 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Line Rated Current	16 A
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	8 IEC 60320 C13
--------------------------------	-----------------

Conformance

Product Certifications	CUL Listed C-tick CE CSA GOST UL Listed VCCI VDE
Standards	FCC Part 15 class A ICES-003 UL 60950

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304331513
Package weight(Lbs)	6.44 lb(US) (2.92 kg)

Packing Units

Package 1 Height	2.52 in (6.4 cm)
Package 1 width	18.50 in (47 cm)
Package 1 Length	13.27 in (33.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------