



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided Equipment	Cord retention bracket(s) Horizontal mounting brackets User Manual Installation guide
--------------------	--

Physical

Cable length	12 ft (3.66 m)
Color	Black
Depth	4.25 in (10.8 cm)
Height	1.73 in (4.4 cm)
Product Weight	5.00 lb(US) (2.27 kg)
Width	17.52 in (44.5 cm)

Input

Line Rated Current	16 A
Permissible voltage	100...120 V
Input current limits	20 A
Load Capacity	1900 VA
Input Frequency	50/60 Hz
Plug standard	NEMA L5-20P
Nominal Input Voltage	100 V 120 V

Output

Number of power socket outlets	8 NEMA 5-20R
--------------------------------	--------------

Conformance

Product Certifications	CUL Listed CSA Industry Canada UL Listed
Standards	FCC Part 15 class A ICES-003 UL 60950

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Package weight(Lbs)	7.61 lb(US) (3.45 kg)
---------------------	-----------------------

Packing Units

Package 1 Height	2.76 in (7 cm)
Package 1 width	18.50 in (47 cm)
Package 1 Length	13.50 in (34.3 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------