



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	3 phase
Main Output Voltage	208 V
Number of rack unit	0U
Cable length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Documentation CD Installation guide Rack Mounting brackets RS-232 configuration cable Toolless Mounting Kit

Physical

Color	Black
Height	70.00 in (177.8 cm)
Width	2.20 in (5.6 cm)
Depth	3.50 in (8.9 cm)
Net Weight	21.32 lb(US) (9.67 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Max line current	35 A
Input current limits	35 A
Load Capacity	12500 VA
Input Frequency	50/60 Hz
Number of input connectors	1 CS8365

Output

Number of power socket outlets	21 IEC 60320 C13 3 IEC 60320 C19
--------------------------------	-------------------------------------

Conformance

Product Certifications	CUL Listed CSA Industry Canada UL Listed
Standards	FCC Part 15 class A ICES-003 UL 60950

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304331667
Package weight(Lbs)	28.44 lb(US) (12.9 kg)

Packing Units

Package 1 Height	82.99 in (210.8 cm)
Package 1 width	5.98 in (15.2 cm)
Package 1 Length	5.00 in (12.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------