

AP8641WHT

Rack PDU 2G, Metered by Outlet with Switching, ZeroU, 30A, 200/208V, (21) C13 & (3) C19, Full white

Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided Equipment	CAN Port Terminator Installation guide Rack Mounting brackets Safety guide Serial configuration cable
--------------------	---

Physical

Cable length	9.84 ft (3.00 m)
Color	Black
Depth	2.01 in (5.1 cm)
Height	72.01 in (182.9 cm)
Product Weight	18.14 lb(US) (8.23 kg)
Width	2.20 in (5.6 cm)

Input

Input Frequency	50/60 Hz
Line Rated Current	24 A
Plug standard	NEMA L6-30P
Number of cables	1
Permissible voltage	200...240 V
Max line current	30 A
Input current limits	30 A
Nominal Input Voltage	200 V 208 V 230 V

Output

Max current draw	30 A
Number of power socket outlets	21 IEC 60320 C13 3 IEC 60320 C19
Protection Type	Circuit breaker
Output voltage	200 V 208 V

Conformance

Product Certifications	CUL Listed PSE UL Listed VCCI Class A
Standards	FCC Part 15 class A ICES-003

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Package weight(Lbs)	23.15 lb(US) (10.5 kg)
---------------------	------------------------

Packing Units

Package 1 Height	80.24 in (203.8 cm)
Package 1 width	6.38 in (16.2 cm)
Package 1 Length	4.65 in (11.8 cm)
Number of Units in Package 3	48

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------