

Product data sheet

Characteristics

AP8864X630

Rack PDU 2G, Metered, ZeroU, 8.7kW, 208V, (36) C13 & (6) C19, L15-30P input, 3m length



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

Physical

Depth	2.01 in (5.1 cm)
Height	72.01 in (182.9 cm)
Product Weight	19.22 lb(US) (8.72 kg)
Width	2.20 in (5.6 cm)

Conformance

Product Certifications	UL Listed
------------------------	-----------

Environmental

Ambient Air Temperature for Operation	32...131 °F (0...55 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304321804
Package weight(Lbs)	25.31 lb(US) (11.48 kg)

Packing Units

Package 1 Height	80.71 in (205 cm)
Package 1 width	6.69 in (17 cm)
Package 1 Length	4.41 in (11.2 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available