



### Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

### Main

|                     |                                                                                            |
|---------------------|--------------------------------------------------------------------------------------------|
| Main Input Voltage  | 3 phase                                                                                    |
| Main Output Voltage | 208 V                                                                                      |
| Plug standard       | IEC 60309 60 A 3P+PE                                                                       |
| Number of rack unit | 0U                                                                                         |
| Cable length        | 6 ft (1.83 m)                                                                              |
| Number of cables    | 1                                                                                          |
| Provided Equipment  | Installation guide<br>Rack Mounting brackets<br>Serial configuration cable<br>Safety guide |

### Physical

|                     |                        |
|---------------------|------------------------|
| Color               | Black                  |
| Height              | 72.01 in (182.9 cm)    |
| Width               | 2.20 in (5.6 cm)       |
| Depth               | 2.01 in (5.1 cm)       |
| Net Weight          | 22.49 lb(US) (10.2 kg) |
| Mounting Location   | Side                   |
| Mounting preference | No preference          |
| Mounting Mode       | Not rack-mountable     |

### Input

|                      |          |
|----------------------|----------|
| Line Rated Current   | 48 A     |
| Max line current     | 48 A     |
| Input current limits | 60 A     |
| Load Capacity        | 17300 VA |
| Input Frequency      | 50/60 Hz |

### Output

|                                |                  |
|--------------------------------|------------------|
| Number of power socket outlets | 30 IEC 60320 C13 |
|--------------------------------|------------------|

## Conformance

|                        |                                                                                     |
|------------------------|-------------------------------------------------------------------------------------|
| Product Certifications | CUL Listed<br>UL Listed<br>VCCI Class A                                             |
| Standards              | EN 55022 Class A<br>EN 55024<br>EN 61000-3-2<br>EN 61000-3-3<br>FCC Part 15 class A |

## Environmental

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 23...140 °F (-5...60 °C)         |
| Relative Humidity                     | 5...95 %                         |
| Operating altitude                    | 0...10000 ft                     |
| Ambient Air Temperature for Storage   | -13...149 °F (-25...65 °C)       |
| Storage Relative Humidity             | 5...95 %                         |
| Storage altitude                      | 0...50000 ft (0.00...15240.00 m) |

## Ordering and shipping details

|                     |                         |
|---------------------|-------------------------|
| GTIN                | 731304289913            |
| Package weight(Lbs) | 30.97 lb(US) (14.05 kg) |

## Packing Units

|                  |                     |
|------------------|---------------------|
| Package 1 Height | 84.61 in (214.9 cm) |
| Package 1 width  | 8.70 in (22.1 cm)   |
| Package 1 Length | 4.41 in (11.2 cm)   |

## Offer Sustainability

|                             |                                               |
|-----------------------------|-----------------------------------------------|
| Sustainable offer status    | Green Premium product                         |
| REACH Regulation            | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive           | Compliant <a href="#">EU RoHS Declaration</a> |
| Lead free                   | Yes                                           |
| Mercury free                | Yes                                           |
| RoHS exemption information  | <a href="#">Yes</a>                           |
| Environmental Disclosure    | <a href="#">Product Environmental Profile</a> |
| Circularity Profile         | <a href="#">End Of Life Information</a>       |
| Optimized Energy Efficiency | Energy efficient product                      |
| Take-back                   | Take-back program available                   |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|