



Overview

Presentation	APC Metered Rack Power Distribution Units (PDUs) provide active metering to enable energy optimization and circuit protection. User-defined alarm thresholds mitigate risk with real-time local and remote alerts to warn of potential circuit overloads. Metered Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency.
Lead time	Usually in Stock

Main

Main Input Voltage	120 V 208 V
PDU Type	Metered
Main Output Voltage	120 V
Other Output Voltage	240 V
Input Connection Type	NEMA L14-30P
Number of rack unit	0U
Cable length	9.84 ft (3.00 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets Serial configuration cable Safety guide

Physical

Color	Black
Height	70.51 in (179.1 cm)
Width	2.17 in (5.5 cm)
Depth	1.73 in (4.4 cm)
Net Weight	14.07 lb(US) (6.38 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Mounting position	Vertical

Input

Line Rated Current	24 A
Input current limits	30 A
Load Capacity	4992 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	16 NEMA 5-20R 12 IEC 60320 C13 2 IEC 60320 C19
--------------------------------	--

Conformance

Product Certifications	CUL Listed UL Listed
Standards	FCC Part 15 class A ICES-003 UL 60950-1

Environmental

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304307501
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	78.98 in (200.6 cm)
Package 1 Width	4.26 in (10.83 cm)
Package 1 Length	6.48 in (16.47 cm)
Package 1 Weight	15.85 lb(US) (7.19 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------