



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided Equipment	Installation guide Rack Mounting brackets Safety guide Serial configuration cable
--------------------	--

Physical

Cable length	6 ft (1.83 m)
Color	Black
Depth	2.64 in (6.7 cm)
Height	72.01 in (182.9 cm)
Product Weight	22.00 lb(US) (9.98 kg)
Width	2.20 in (5.6 cm)

Input

Input Frequency	50/60 Hz
Line Rated Current	24 A
Plug standard	NEMA L21-30P
Number of cables	1
Max line current	30 A
Input current limits	30 A
Nominal Input Voltage	3 phase

Output

Max current draw	30 A
Number of power socket outlets	21 IEC 60320 C13 3 IEC 60320 C19
Protection Type	Circuit breaker
Output voltage	208 V

Conformance

Product Certifications	CUL Listed UL Listed VCCI Class A
Standards	FCC Part 15 class A ICES-003

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Package weight(Lbs)	25.00 lb(US) (11.34 kg)
---------------------	-------------------------

Packing Units

Package 1 Height	83.74 in (212.7 cm)
Package 1 width	10.75 in (27.3 cm)
Package 1 Length	3.74 in (9.5 cm)
Number of Units in Package 3	48

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------