



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided Equipment	Installation guide Rack Mounting brackets Safety guide Serial configuration cable
--------------------	--

Physical

Cable length	10 ft (3.05 m)
Color	Black
Depth	1.81 in (4.6 cm)
Height	72.01 in (182.9 cm)
Product Weight	17.95 lb(US) (8.14 kg)
Width	2.17 in (5.5 cm)

Input

Input Frequency	50/60 Hz
Line Rated Current	24 A
Plug standard	NEMA L14-30P
Number of cables	1
Input current limits	30 A
Load Capacity	5760 VA
Nominal Input Voltage	120 V 208 V

Output

Max current draw	24 A
Number of power socket outlets	16 NEMA 5-20R 7 IEC 60320 C13 1 IEC 60320 C19
Protection Type	Circuit breaker
Output voltage	120 V 208 V

Conformance

Product Certifications	CUL Listed UL Listed
Standards	FCC Part 15 class A ICES-003 UL 60950-1

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Package weight(Lbs)	22.53 lb(US) (10.22 kg)
---------------------	-------------------------

Packing Units

Package 1 Height	80.35 in (204.1 cm)
Package 1 width	6.48 in (16.47 cm)
Package 1 Length	4.69 in (11.92 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------