



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	120 V 208 V 230 V
Main Output Voltage	120 V 208 V 230 V
Input Connection Type	IEC 60320 C20
Number of rack unit	1U
Cable length	8.2 ft (2.50 m)
Number of cables	1
Provided Equipment	User Manual Rack Mounting brackets

Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	17.60 in (44.7 cm)
Depth	2.24 in (5.7 cm)
Net Weight	2.16 lb(US) (0.98 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Acceptable Input Voltage	90...250 V
Max line current	16 A
Input current limits	16 A
Load Capacity	3680 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	10 IEC 60320 C13 2 IEC 60320 C19
--------------------------------	-------------------------------------

Conformance

Product Certifications	CUL Listed CE UL Listed VDE Victoria
------------------------	--

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304123521
Package weight(Lbs)	5.20 lb(US) (2.36 kg)

Packing Units

Package 1 Height	6.50 in (16.5 cm)
Package 1 width	19.02 in (48.3 cm)
Package 1 Length	5.98 in (15.2 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------