



Overview

Presentation	Reliable rack power distribution designed to increase manageability and efficiency in the data center The output and input connections are (10) C13 Real-time remote monitoring of connected loads User-defined alarms warn IT and data center managers of potential circuit overloads to prevent accidental power loss to critical equipment.
Lead time	Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
PDU Type	Basic
Main Output Voltage	208 V
Input Connection Type	NEMA L6-30P
Number of rack unit	1U
Cable length	12 ft (3.66 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets User Manual

Physical

Color	Black
Height	1.73 in (4.4 cm)
Width	17.52 in (44.5 cm)
Depth	3.03 in (7.7 cm)
Net Weight	5.62 lb(US) (2.55 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted
Mounting position	Horizontal

Input

Line Rated Current	24 A
Acceptable Input Voltage	200...240 V
Max line current	30 A
Input current limits	30 A
Load Capacity	4992 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	10 IEC 60320 C13
--------------------------------	------------------

Conformance

Product Certifications	CUL Listed PSE UL Listed
Standards	UL 60950

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...15000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304272755
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.73 in (17.1 cm)
Package 1 Width	6.85 in (17.4 cm)
Package 1 Length	19.02 in (48.3 cm)
Package 1 Weight	8.02 lb(US) (3.64 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------