



### Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

### Main

|                    |                                                                                                |
|--------------------|------------------------------------------------------------------------------------------------|
| Battery Type       | Lead-Acid battery                                                                              |
| Provided Equipment | All required connectors<br>Battery recycling guide<br>Installation guide<br>Reusable packaging |

### Physical

|               |                         |
|---------------|-------------------------|
| Height        | 2.99 in (7.6 cm)        |
| Width         | 7.99 in (20.3 cm)       |
| Depth         | 22.99 in (58.4 cm)      |
| Net Weight    | 49.01 lb(US) (22.23 kg) |
| Mounting Mode | Not rack-mountable      |

### Environmental

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 32...104 °F (0...40 °C)          |
| Operating altitude                    | 0...10000 ft                     |
| Relative Humidity                     | 0...95 %                         |
| Ambient Air Temperature for Storage   | 5...113 °F (-15...45 °C)         |
| Storage altitude                      | 0...50000 ft (0.00...15240.00 m) |
| Storage Relative Humidity             | 0...95 %                         |

### Batteries & Runtime

|                           |                            |
|---------------------------|----------------------------|
| Battery blocks per string | 10                         |
| Battery Slots Empty       | 0                          |
| Included Battery Modules  | 0                          |
| Device mounting           | Enclosed battery cartridge |
| Battery Voltage           | 120 V                      |
| RBC Quantity              | 1                          |

### Ordering and shipping details

|                     |                         |
|---------------------|-------------------------|
| GTIN                | 731304356165            |
| Package weight(Lbs) | 55.40 lb(US) (25.13 kg) |

### Packing Units

|                              |                    |
|------------------------------|--------------------|
| Package 1 Height             | 8.98 in (22.8 cm)  |
| Package 1 width              | 15.47 in (39.3 cm) |
| Package 1 Length             | 29.96 in (76.1 cm) |
| Number of Units in Package 3 | 12                 |

### Offer Sustainability

|                   |                                            |
|-------------------|--------------------------------------------|
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
|-------------------|--------------------------------------------|

### Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|