



### Overview

|              |                                                                                    |
|--------------|------------------------------------------------------------------------------------|
| Presentation | Enables users to mount equipment with different depths in a 48U, 600 mm enclosure. |
| Lead time    | Usually in Stock                                                                   |

### Main

|                    |                                                                   |
|--------------------|-------------------------------------------------------------------|
| Number of cables   | 1                                                                 |
| Provided equipment | Installation guide<br>Mounting Hardware<br>Rack mounting hardware |

### Physical

|                     |                      |
|---------------------|----------------------|
| Color               | Black                |
| Height              | 44.80 in (113.8 cm)  |
| Width               | 2.87 in (7.3 cm)     |
| Depth               | 2.32 in (5.9 cm)     |
| Net Weight          | 9.04 lb(US) (4.1 kg) |
| Mounting preference | No preference        |
| Mounting Mode       | Not rack-mountable   |

### Ordering and shipping details

|                     |                        |
|---------------------|------------------------|
| GTIN                | 731304234647           |
| Package weight(Lbs) | 12.52 lb(US) (5.68 kg) |

### Packing Units

|                  |                     |
|------------------|---------------------|
| Package 1 Height | 45.51 in (115.6 cm) |
| Package 1 width  | 5.00 in (12.7 cm)   |
| Package 1 Length | 4.02 in (10.2 cm)   |

### Offer Sustainability

|                          |                                                                                 |
|--------------------------|---------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product                                                           |
| REACH Regulation         | REACH Declaration                                                               |
| REACH free of SVHC       | Yes                                                                             |
| EU RoHS Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free   | Yes                                                                             |
| Mercury free             | Yes                                                                             |

|                             |                                                                                      |
|-----------------------------|--------------------------------------------------------------------------------------|
| RoHS exemption information  |  Yes |
| Take-back                   | Take-back program available                                                          |
| <b>Contractual warranty</b> |                                                                                      |
| Warranty                    | 2 years repair or replace                                                            |