



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided Equipment	User Manual
--------------------	-------------

Physical

Depth	9.02 in (22.9 cm)
Height	8.07 in (20.5 cm)
Product Weight	36.60 lb(US) (16.6 kg)
Width	5.43 in (13.8 cm)

Conformance

Product Certifications	UL Recognized
Marking	CE Mark

Environmental

Ambient Air Temperature for Operation	32...122 °F (0...50 °C)
Ambient Air Temperature for Storage	-4...122 °F (-20...50 °C)

Batteries & Runtime

Battery blocks per string	4
Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Stand alone battery stack
Battery Voltage	12 V
Battery Type	Gel Cell

Ordering and shipping details

Package weight(Lbs)	38.01 lb(US) (17.24 kg)
---------------------	-------------------------

Packing Units

Package 1 Height	10.98 in (27.9 cm)
Package 1 width	6.50 in (16.5 cm)
Package 1 Length	10.00 in (25.4 cm)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------