



Main

Product or Component Type	Full voltage starter
Range of product	Instakits
Disconnecter device type	Non-fusible disconnect

Complementary

Line Rated Current	9 A
Maximum Horse Power Rating	0.3 Hp 120 V AC, 1 phase 1 Hp 240 V AC, 1 phase 2 Hp 208 V AC, 3 phase 2 Hp 230 V AC, 3 phase 5 Hp 460 V AC, 3 phase 7.5 hp 575 V AC, 3 phase
[Ue] rated operational voltage	120 V AC 50/60 Hz
Motor starter type	Reversing
Protection Type	Switch-disconnector fuse
Location of connection	Line
[Uc] control circuit voltage	120 V AC

Environment

Product Certifications	CSA UL IEC
NEMA degree of protection	NEMA 1 steel

Ordering and shipping details

Category	22313 - CTRS,D-LINE,ENCL (METAL)
Discount Schedule	I11
GTIN	00785901631996
Nbr. of units in pkg.	1
Package weight(Lbs)	14.51 lb(US) (6.58 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.59 in (26.9 cm)
Package 1 width	11.30 in (28.7 cm)
Package 1 Length	15.31 in (38.9 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------