

PDPM150G6F

APC 144kVA Modular Power Distribution Unit,
Isolation Transformer, 480:208V, 72 Poles, 2
Subfeed



Overview

Presentation	A fully scalable power distribution system that cost-effectively provides high levels of availability and enables the quick addition of circuits and cord-sets.
Lead time	Usually Ships within 6 Weeks

Main

Main Input Voltage	3 phase
Main Output Voltage	208 V 3 phase
Provided Equipment	Installation guide Network Management Card

Physical

Color	Black
Height	79.02 in (200.7 cm)
Width	23.62 in (60 cm)
Depth	42.09 in (106.9 cm)
Net Weight	1843.07 lb(US) (836 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	60 Hz
Max line current	178 A
Load Capacity	144000 VA

Output

Protection Type	Circuit breaker
-----------------	-----------------

Conformance

Product Certifications	CUL Listed CSA
Standards	OSHPD UL 60950-1

Environmental

Ambient Air Temperature for Operation	23...104 °F (-5...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...9842 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304295396
Package weight(Lbs)	1944.48 lb(US) (882 kg)

Packing Units

Package 1 Height	84.76 in (215.3 cm)
Package 1 width	40.00 in (101.6 cm)
Package 1 Length	47.99 in (121.9 cm)

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------