



Overview

Presentation	Extended run power protection for servers, networks, and telecommunications
Lead time	Usually in Stock

Main

Number of rack unit	0U
Number of cables	1
Battery Type	Lead-Acid battery

Physical

Height	5.31 in (13.5 cm)
Width	6.50 in (16.5 cm)
Depth	23.11 in (58.7 cm)
Net Weight	62.13 lb(US) (28.18 kg)
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 %
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 %

Batteries & Runtime

Battery Placement	Internal Battery
Battery Slots Empty	0
Included Battery Modules	0
Battery Life	3...5 year(s)
RBC Quantity	1
Battery Volt-Amp-Hour Capacity	808 VAh

Ordering and shipping details

GTIN	731304108320
Package weight(Lbs)	69.14 lb(US) (31.36 kg)

Packing Units

Package 1 Height	17.28 in (43.9 cm)
Package 1 width	12.99 in (33 cm)
Package 1 Length	31.10 in (79 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace, optional on-site warranties available, optional extended warranties available
----------	--