



### Main

|                           |                                                           |
|---------------------------|-----------------------------------------------------------|
| Range                     | TeSys                                                     |
| Product name              | TeSys LE                                                  |
| Device short name         | LE1D                                                      |
| Product or Component Type | Enclosed DOL starter                                      |
| Device Application        | Standard                                                  |
| Utilisation category      | AC-3                                                      |
| Device composition        | Thermal overload relay ordered separately<br>Contactor    |
| Control type              | Push-button start Green I<br>Push-button stop/reset Red O |

### Complementary

|                                             |                                                                                                                                                                          |
|---------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [Ith] Conventional free air thermal current | 18 A AC-3                                                                                                                                                                |
| Motor power kW                              | 10 KW 500 V AC 50/60 Hz<br>10 KW 660/690 V AC 50/60 Hz<br>4 KW 220/230 V AC 50/60 Hz<br>9 KW 415 V AC 50/60 Hz<br>9 KW 440 V AC 50/60 Hz<br>7.5 kW 380/400 V AC 50/60 Hz |
| [Ith] Conventional free air thermal current | 17 A                                                                                                                                                                     |
| [Uc] control circuit voltage                | 220 V AC 50/60 Hz                                                                                                                                                        |
| Cable entry number                          | 2 ISO20 top<br>2 ISO20 bottom<br>2 Pg 16 bottom<br>2 ISO25 top<br>2 Pg 21 bottom<br>2 ISO25 bottom                                                                       |
| Width                                       | 3.98 in (101 mm)                                                                                                                                                         |
| Height                                      | 7.91 in (201 mm)                                                                                                                                                         |
| Depth                                       | 6.04 in (153.5 mm)                                                                                                                                                       |
| Product Weight                              | 2.24 lb(US) (1.015 kg)                                                                                                                                                   |

### Environment

|                                       |                          |
|---------------------------------------|--------------------------|
| Material                              | Polycarbonate            |
| IP degree of protection               | IP65 IEC 60529           |
| IK degree of protection               | IK07 IEC 60529           |
| Standards                             | IEC 60947-4-1            |
| Ambient air temperature for operation | 23...104 °F (-5...40 °C) |
| Environmental characteristic          | Standard environment     |

### Ordering and shipping details

|                       |                                  |
|-----------------------|----------------------------------|
| Category              | 22313 - CTRS,D-LINE,ENCL (METAL) |
| Discount Schedule     | I11                              |
| GTIN                  | 3389110578188                    |
| Nbr. of units in pkg. | 1                                |
| Package weight(Lbs)   | 2.56 lb(US) (1.161 kg)           |
| Returnability         | No                               |
| Country of origin     | FR                               |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Package 1 Height             | 6.54 in (16.6 cm)       |
| Package 1 width              | 7.87 in (20 cm)         |
| Package 1 Length             | 9.92 in (25.2 cm)       |
| Unit Type of Package 2       | P06                     |
| Number of Units in Package 2 | 22                      |
| Package 2 Weight             | 85.16 lb(US) (38.63 kg) |
| Package 2 Height             | 28.94 in (73.5 cm)      |
| Package 2 width              | 23.62 in (60 cm)        |
| Package 2 Length             | 31.50 in (80 cm)        |
| Package 3 Height             | 31.50 in (80 cm)        |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                           |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                     |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                         |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                       |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                             |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                       |
| Mercury free               | Yes                                                                                                                                                                                                                                                       |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                       |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                    |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                             |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                              |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|