



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1D
Product or Component Type	Enclosed DOL starter
Device Application	Standard
Utilisation category	AC-3
Device composition	Thermal overload relay ordered separately Contactor
Control type	Push-button start Green I Push-button stop/reset Red O

Complementary

[Ith] Conventional free air thermal current	18 A AC-3
Motor power kW	10 KW 500 V AC 50/60 Hz 10 KW 660/690 V AC 50/60 Hz 4 KW 220/230 V AC 50/60 Hz 9 KW 415 V AC 50/60 Hz 9 KW 440 V AC 50/60 Hz 7.5 kW 380/400 V AC 50/60 Hz
[Ith] Conventional free air thermal current	17 A
[Uc] control circuit voltage	230 V AC 50/60 Hz
Cable entry number	2 ISO20 top 2 ISO20 bottom 2 Pg 16 bottom 2 ISO25 top 2 Pg 21 bottom 2 ISO25 bottom
Width	3.98 in (101 mm)
Height	7.91 in (201 mm)
Depth	6.04 in (153.5 mm)
Product Weight	2.24 lb(US) (1.015 kg)

Environment

Material	Polycarbonate
IP degree of protection	IP65 IEC 60529
IK degree of protection	IK07 IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	23...104 °F (-5...40 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22313 - CTRS,D-LINE,ENCL (METAL)
Discount Schedule	I11
GTIN	3389110541366
Nbr. of units in pkg.	1
Package weight(Lbs)	2.60 lb(US) (1.179 kg)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	6.30 in (16 cm)
Package 1 width	7.87 in (20 cm)
Package 1 Length	9.84 in (25 cm)
Unit Type of Package 2	P06
Number of Units in Package 2	22
Package 2 Weight	88.05 lb(US) (39.94 kg)
Package 2 Height	31.50 in (80 cm)
Package 2 width	31.50 in (80 cm)
Package 2 Length	23.62 in (60 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------