



Main

Range of Product	Altivar
Accessory / separate part category	Mounting and fixing accessory
Accessory / Separate Part Type	Mounting kit
Product compatibility	ATV61H075M3 ATV61H075N4 ATV61HU15M3 ATV61HU15N4 ATV61HU22N4 ATV71H037M3 ATV71H075M3 ATV71H075N4 ATV71HU15M3 ATV71HU15N4 ATV71HU22N4
Accessory / separate part destination	Variable speed drive
Range Compatibility	Altivar 71 Altivar 61
Product Specific Application	For mounting the drive power section outside the enclosure

Complementary

Kit composition	1 cutting and drilling template 1 fan support 1 user manual 1 metal frame of the right size for drive rating Corner pieces Fixing accessories seals
Net Weight	5.95 lb(US) (2.7 kg)

Environment

Environmental characteristic	Dust and damp proof
------------------------------	---------------------

Ordering and shipping details

Category	22000-Temporary Category for ITS Price Promotion
Discount Schedule	I
GTIN	3389119200707
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.30 in (16.000 cm)
Package 1 Width	9.65 in (24.500 cm)
Package 1 Length	16.54 in (42.000 cm)
Package 1 Weight	6.53 lb(US) (2.964 kg)
Unit Type of Package 2	P06
Number of Units in Package 2	9

Package 2 Height	28.94 in (73.500 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	23.62 in (60.000 cm)
Package 2 Weight	87.47 lb(US) (39.676 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------