

# Product data sheet

Specifications



license, Ecostruxure Machine Expert, addon, Asi safety, node locked, team, 10 users

ESESADCZZTPAZZ

## Main

|                              |                                                                                                               |
|------------------------------|---------------------------------------------------------------------------------------------------------------|
| Range of product             | EcoStruxure Machine Expert                                                                                    |
| Product or component type    | License                                                                                                       |
| Format                       | Digital                                                                                                       |
| Software type                | Add-on                                                                                                        |
| Type of license              | Node locked license                                                                                           |
| Variant                      | ASi safety                                                                                                    |
| Software version             | V2.2                                                                                                          |
| Operating system requirement | Windows 10 32/64 bit<br>Windows 11 32/64 bit                                                                  |
| User language                | English<br>Spanish<br>Chinese<br>French<br>German<br>Italian<br>Portuguese (Brazilian)<br>Turkish<br>Japanese |

## Complementary

|                   |                                       |
|-------------------|---------------------------------------|
| License category  | Permanent                             |
| Software function | Engineering<br>Programming safety PLC |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                             |                                               |
|-----------------------------|-----------------------------------------------|
| Range compatibility         | Modicon M241                                  |
|                             | Modicon M251                                  |
|                             | Modicon M262                                  |
|                             | Modicon TM3                                   |
|                             | Modicon TM5                                   |
|                             | Modicon TM7                                   |
|                             | PacDrive LMC Eco                              |
|                             | PacDrive LMC Pro                              |
|                             | PacDrive LMC Pro2                             |
|                             | Preventa XPSMC                                |
|                             | Preventa XPSMCM                               |
|                             | Lexium 32                                     |
|                             | Lexium 32i                                    |
|                             | Lexium 32M                                    |
|                             | Lexium 52                                     |
|                             | Lexium 62                                     |
|                             | Lexium ILA                                    |
|                             | Lexium ILE                                    |
|                             | Lexium ILS                                    |
|                             | Lexium SD3                                    |
|                             | Altivar 320                                   |
|                             | Altivar 340                                   |
|                             | Altivar Process ATV600                        |
|                             | Altivar Easy 610                              |
|                             | Altivar 660 Drive System                      |
|                             | Altivar Process ATV900                        |
|                             | Altivar Process 980 Regenerative Drive System |
|                             | Harmony XB5R                                  |
|                             | Harmony XB4R                                  |
|                             | OsiSense XG                                   |
|                             | OsiSense XUW                                  |
|                             | TeSys U                                       |
|                             | TeSys T                                       |
|                             | TeSys island                                  |
|                             | Magelis XBT GH                                |
|                             | Magelis GTO                                   |
|                             | Magelis GTU                                   |
|                             | Magelis GTUX                                  |
|                             | Magelis iPC                                   |
|                             | Magelis STO & STU                             |
|                             | Magelis GK                                    |
|                             | Magelis SCU                                   |
|                             | EcoStruxure Machine Expert Twin               |
| Communication port protocol | Modbus SL                                     |
|                             | Modbus TCP                                    |
|                             | EtherNet/IP                                   |
|                             | CANopen                                       |
|                             | Sercos III                                    |
|                             | CANmotion                                     |
| Hosting option              | On-premise                                    |
| License size                | Team (10 users)                               |
| System requirements         | 8 GB RAM                                      |
|                             | 15 GB hard disk space                         |
| Processor requirement       | Intel Core 2 Duo                              |
| Display resolution          | 1280 x 1024 pixels                            |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Weight             | 0.001 g |