

Product data sheet

Specifications



Wall mounted steel enclosure,
PanelSeT S3D, plain door, without
mounting plate, 400x600x200mm,
IP66, IK10

NSYS3D4620

**Product availability: Non-Stock - Not normally stocked in
distribution facility**

Main

Range	PanelSeT
Product name	PanelSeT S3D
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	15.7 in (400 mm)
Enclosure nominal width	23.6 in (600 mm)
Enclosure nominal depth	7.9 in (200 mm)
Door type	Solid
Mounting plate description	Without mounting plate
Type of gland plate	Standard
Installation accessory type	Wall-mounting
Device composition	1 body 1 door 1 lock 1 cable gland plate

Complementary

body type	Single piece body Gutter-shaped front rail double sheet thickness
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	3 points lock, 3 mm double-bar
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws
Material	steel
Surface finish	epoxy-polyester powder
color	Gray RAL 7035)
Standards	IEC 62208 UL CUL
Product Certifications	cUL BV GL UL DNV

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Weight	23.1 lb(US) (10.5 kg)
----------------	-----------------------

Environment

NEMA Degree of Protection	NEMA 4X/13
IK degree of protection	IK10 IEC 62262
IP degree of protection	IP66 IEC 60529

Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
GTIN	3606480159541
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	9.65 in (24.500 cm)
Package 1 Width	16.54 in (42.000 cm)
Package 1 Length	24.41 in (62.000 cm)
Package weight(Lbs)	23.065 lb(US) (10.462 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	30
Package 2 Height	78.74 in (200.000 cm)
Package 2 Width	39.37 in (100.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	742.958 lb(US) (337.000 kg)

Contractual warranty

Coverage	Core product
Warranty	18 months

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	99
Environmental Disclosure	Product Environmental Profile

Use Better


Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	E893f0a0-d2cc-4011-9425-3873dde70142
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features



Sturdy components' protection



Earthing studs included



Large choice of dimensions & accessories



Quality & aesthetics



Easy to equip
Easy to maintain



Reusable eco-friendly packaging

