

Product data sheet

Specifications



TeSys SK, auxiliary contact block, 2 NC

LA1SK02

Product availability: Stock - Normally stocked in distribution facility

Main

Range	TeSys
Device short name	LA1SK
Product or Component Type	Auxiliary contact block
Product Compatibility	LC1SK
Auxiliary contacts operation	Instantaneous
Pole contact composition	2 NC
Connections - terminals	screw clamp terminals 1 0.002...0.009 in² (1.5...6 mm²)solid screw clamp terminals 2 0.002...0.006 in² (1.5...4 mm²)solid screw clamp terminals 1 0.0008...0.009 in² (0.5...6 mm²)flexible with cable end screw clamp terminals 2 0.0005...0.004 in² (0.35...2.5 mm²)flexible with cable end screw clamp terminals 1 0.0005...0.009 in² (0.35...6 mm²)flexible without cable end screw clamp terminals 2 0.0005...0.002 in² (0.35...1.5 mm²)flexible without cable end

Complementary

Mounting Location	Front side
[Ui] rated insulation voltage	690 V IEC 60947 690 V BS 5424 690 V VDE 0110 group C 690 V CSA C22.2 No 14
[Ue] rated operational voltage	690 V AC <= 400 Hz
[Ith] conventional free air thermal current	10 A (at 131 °F (55 °C))
Associated fuse rating	10 A gL conforming to IEC 60947 10 A gL conforming to VDE 0660
Tightening torque	7.08 lbf.in (0.8 N.m) screw clamp terminals
Width	1.06 in (27 mm)
Product Weight	0.049 lb(US) (0.022 kg)

Environment

Standards	CSA C22.2 No 60947-5-1 EN/IEC 60947-5-1 UL 60947-5-1
Product Certifications	CB Scheme CE UKCA EAC cULus
IP degree of protection	IP2X
Protective treatment	TC IEC 60068
Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature for Storage	-58...158 °F (-50...70 °C)
Operating altitude	6561.68 ft (2000 m) without derating

Ordering and shipping details

Category	US10I1222371
Discount Schedule	0I12
GTIN	3389110573947
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.42 in (3.6 cm)
Package 1 Width	1.65 in (4.2 cm)
Package 1 Length	2.09 in (5.3 cm)
Package weight(Lbs)	1.0 oz (28.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	60
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	3.975 lb(US) (1.803 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	C39a7e5e-6a28-4540-b3bb-b5a727bdce6a

Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.