



Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Non reversing
Line Rated Current	18 A
Number of Poles	3P
Horsepower Rating	5 Hp 460 V AC, 3 phase 5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Control Units	No control units
Auxiliary Contacts	Without
Thermal overload type	Solid state Motor Logic class 10/20 3...9 A
Disconnect Type	Fusible disconnect switch H and K, 30 A
NEMA size	0
Height	24 in (609.60 mm)
Depth	8.34 in (211.84 mm)
Width	9.5 in (241.30 mm)
Handle Swing	3.25 in (82.55 mm)

Environment

Enclosure Type	NEMA 12 painted sheet steel with external reset
Product Certifications	CSA UL Listed

Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
GTIN	NULL
Nbr. of units in pkg.	1
Package weight(Lbs)	45 lb(US) (20.41 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Under investigation

Contractual warranty

Warranty	18 months
----------	-----------