



## Main

|                           |                                      |
|---------------------------|--------------------------------------|
| Product or Component Type | Electrically Held Lighting Contactor |
| Range of Product          | 8903L                                |
| Control Circuit           | Separate control circuit             |

## Complementary

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Control Circuit Voltage         | 110 V AC 50 Hz<br>120 V AC 60 Hz  |
| Inrush power in VA              | 150 VA 60 Hz<br>140 VA 50 Hz      |
| Hold-in power consumption in VA | 30 VA 60 Hz<br>30 VA 50 Hz        |
| Current Rating                  | 20 A tungsten<br>30 A fluorescent |
| Number of Poles                 | 6P 6 NO                           |
| Control Unit                    | No control units                  |
| Pilot Light                     | No indicator                      |
| Electrical Connection           | Screw-clamp terminals             |
| Height                          | 15.75 in (400 mm)                 |
| Depth                           | 8.50 in (216 mm)                  |
| Width                           | 8.11 in (206 mm)                  |

## Environment

|                        |                                     |
|------------------------|-------------------------------------|
| Enclosure Type         | NEMA 12 painted sheet steel surface |
| Product Certifications | UL Listed<br>CSA                    |

## Ordering and shipping details

|                       |                        |
|-----------------------|------------------------|
| Category              | 21321-8903 L (NOT LX)  |
| Discount Schedule     | CP1                    |
| GTIN                  | 785901022060           |
| Nbr. of units in pkg. | 1                      |
| Package weight(Lbs)   | 21.78 lb(US) (9.88 kg) |
| Returnability         | No                     |
| Country of origin     | MX                     |

## Packing Units

|                        |                   |
|------------------------|-------------------|
| Unit Type of Package 1 | PCE               |
| Package 1 Height       | 15.75 in (40 cm)  |
| Package 1 width        | 8.11 in (20.6 cm) |
| Package 1 Length       | 8.50 in (21.6 cm) |

## Offer Sustainability

|                             |                                                                                                                                 |
|-----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status    | Green Premium product                                                                                                           |
| REACH Regulation            | <a href="#"> REACH Declaration</a>             |
| REACH free of SVHC          | Yes                                                                                                                             |
| EU RoHS Directive           | Compliant <a href="#"> EU RoHS Declaration</a> |
| Toxic heavy metal free      | Yes                                                                                                                             |
| Mercury free                | Yes                                                                                                                             |
| RoHS exemption information  | <a href="#"> Yes</a>                           |
| China RoHS Regulation       | <a href="#"> China RoHS Declaration</a>        |
| Environmental Disclosure    | <a href="#"> Product Environmental Profile</a> |
| PVC free                    | Yes                                                                                                                             |
| Halogen content performance | Halogen free plastic parts product                                                                                              |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|