



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	100 V 120 V
Main Output Voltage	120 V
Plug standard	NEMA L5-30P
Number of rack unit	2U
Cable length	12 ft (3.66 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Installation guide Rack Mounting brackets User Manual

Physical

Height	3.46 in (8.8 cm)
Width	17.48 in (44.4 cm)
Depth	4.41 in (11.2 cm)
Net Weight	7.41 lb(US) (3.36 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Line Rated Current	24 A
Input current limits	30 A
Load Capacity	2880 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	16 NEMA 5-20R
--------------------------------	---------------

Conformance

Product Certifications	CUL Listed CSA UL Listed
Standards	FCC Part 15 class A ICES-003 UL 60950

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304331476
Package weight(Lbs)	11.93 lb(US) (5.41 kg)

Packing Units

Package 1 Height	5.51 in (14 cm)
Package 1 width	20.00 in (50.8 cm)
Package 1 Length	14.49 in (36.8 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------