



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	3 phase
Main Output Voltage	208 V
Number of rack unit	0U
Cable length	10 ft (3.05 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Documentation CD Installation guide Rack Mounting brackets RS-232 configuration cable Toolless Mounting Kit

Physical

Color	Black
Height	70.00 in (177.8 cm)
Width	2.20 in (5.6 cm)
Depth	3.74 in (9.5 cm)
Net Weight	22.84 lb(US) (10.36 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Line Rated Current	40 A
Input current limits	50 A
Load Capacity	14400 VA
Input Frequency	50/60 Hz
Number of input connectors	1 CS8365

Output

Number of power socket outlets	2 NEMA L6-30R 24 IEC 60320 C13 4 IEC 60320 C19
--------------------------------	--

Conformance

Product Certifications	CUL Listed CSA Industry Canada METI Denan UL Listed
Standards	FCC Part 15 class A ICES-003 UL 60950

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304331551
Package weight(Lbs)	31.57 lb(US) (14.32 kg)

Packing Units

Package 1 Height	80.98 in (205.7 cm)
Package 1 width	12.24 in (31.1 cm)
Package 1 Length	3.11 in (7.9 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------