



Overview

Presentation	APC Metered by Outlet Rack Power Distribution Units (PDUs) provide individual outlet power metering to enable energy optimization and circuit protection. Current metering provides real-time remote monitoring of connected loads. Metered by Outlet Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered by Outlet Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered by Outlet Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency.
Lead time	Usually in Stock

Main

Main Input Voltage	200 V 208 V 230 V
PDU Type	Metered outlet
Main Output Voltage	208 V
Input Connection Type	NEMA L6-20P
Number of rack unit	0U
Cable length	9.84 ft (3.00 m)
Provided Equipment	CAN Port Terminator Installation guide Rack Mounting brackets Safety guide Serial configuration cable

Physical

Color	Black
Height	72.01 in (182.9 cm)
Width	2.20 in (5.6 cm)
Depth	2.01 in (5.1 cm)
Net Weight	14.90 lb(US) (6.76 kg)
Mounting Location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted
Mounting position	Vertical

Input

Line Rated Current	16 A
Acceptable Input Voltage	100...240 V
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz

Output

Number of power socket outlets	21 IEC 60320 C13 3 IEC 60320 C19
--------------------------------	-------------------------------------

Conformance

Product Certifications	UL Listed VCCI Class A VDE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 class A ICES-003

Environmental

Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	731304317579
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	80.20 in (203.7 cm)
Package 1 Width	4.61 in (11.7 cm)
Package 1 Length	6.42 in (16.3 cm)
Package 1 Weight	19.91 lb(US) (9.03 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------