

AP8858X852

Rack PDU 2G, Metered, ZeroU, 20A,
200/208V, (36) C13 & (6) C19, 3ft L6-20P Input
Cord



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided Equipment	Installation guide Rack Mounting brackets Safety guide Serial configuration cable
--------------------	--

Physical

Color	Black
Depth	1.73 in (4.4 cm)
Height	70.51 in (179.1 cm)
Product Weight	15.04 lb(US) (6.82 kg)
Width	2.20 in (5.6 cm)

Input

Input Frequency	50/60 Hz
Line Rated Current	16 A
Plug standard	IEC 60320 C20
Permissible voltage	100...240 V
Input current limits	20 A
Nominal Input Voltage	200 V 208 V 230 V

Output

Max current draw	16 A
Number of power socket outlets	36 IEC 60320 C13 6 IEC 60320 C19
Protection Type	Without circuit breaker
Output voltage	100 V 200 V 208 V 230 V

Conformance

Product Certifications	METI Denan VDE
Standards	CSA C22.2 No. 60950 IEC 60950 UL 60950-1

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Package weight(Lbs)	18.61 lb(US) (8.44 kg)
---------------------	------------------------

Packing Units

Package 1 Height	78.74 in (200 cm)
Package 1 width	6.38 in (16.2 cm)
Package 1 Length	4.21 in (10.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------