



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided Equipment	Installation guide Rack Mounting brackets Serial configuration cable Safety guide
--------------------	--

Physical

Cable length	6 ft (1.83 m)
Color	Black
Depth	1.81 in (4.6 cm)
Height	70.51 in (179.1 cm)
Product Weight	16.67 lb(US) (7.56 kg)
Width	2.20 in (5.6 cm)

Input

Line Rated Current	24 A
Max line current	30 A
Input current limits	30 A
Input Frequency	50/60 Hz
Plug standard	NEMA L21-30P
Nominal Input Voltage	3 phase

Output

Number of power socket outlets	2 NEMA 5-20R 36 IEC 60320 C13 6 IEC 60320 C19
--------------------------------	---

Conformance

Standards	CSA C22.2 No. 60950 UL 60950-1
-----------	-----------------------------------

Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

GTIN	00731304329466
Package weight(Lbs)	20.28 lb(US) (9.2 kg)

Packing Units

Package 1 Height	78.74 in (200 cm)
Package 1 width	6.38 in (16.2 cm)
Package 1 Length	4.21 in (10.7 cm)
Number of Units in Package 3	48

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------