



Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Provided Equipment	Installation guide Rack Mounting brackets Serial configuration cable Safety guide
--------------------	--

Physical

Cable length	6 ft (1.83 m)
Color	Black
Depth	2.01 in (5.1 cm)
Height	72.01 in (182.9 cm)
Product Weight	21.16 lb(US) (9.6 kg)
Width	2.20 in (5.6 cm)

Input

Line Rated Current	24 A
Max line current	30 A
Input current limits	30 A
Load Capacity	17300 VA
Input Frequency	50/60 Hz
Plug standard	IEC 60309 30 A 3P+N+E
Nominal Input Voltage	3 phase

Output

Number of power socket outlets	30 IEC 60320 C13 12 IEC 60320 C19
--------------------------------	--------------------------------------

Conformance

Product Certifications	CUL Listed UL Listed VCCI Class A
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 class A ICES-003

Environmental

Ambient Air Temperature for Operation	32...131 °F (0...55 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Package weight(Lbs)	29.98 lb(US) (13.6 kg)
---------------------	------------------------

Packing Units

Package 1 Height	84.61 in (214.9 cm)
Package 1 width	8.70 in (22.1 cm)
Package 1 Length	4.41 in (11.2 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------