



Main

Product or Component Type	Full voltage starter
Range of product	Instakits
Starter Type	Non reversing

Complementary

Control Circuit Voltage	120 V AC 50/60 Hz
Current Rating	50 A
Horsepower Rating	3 Hp 120 V AC, 1 phase 7.5 Hp 240 V AC, 1 phase 15 Hp 208 V AC, 3 phase 15 Hp 230 V AC, 3 phase 40 Hp 460 V AC, 3 phase 40 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Auxiliary Contacts	1 NO + 1 NC
Protection Type	Switch-disconnector fuse
Location of connection	Line

Environment

Product Certifications	UL CSA IEC
Enclosure Type	NEMA 1 steel

Ordering and shipping details

Category	22313 - CTRS,D-LINE,ENCL (METAL)
Discount Schedule	I11
GTIN	785901445500
Nbr. of units in pkg.	1
Package weight(Lbs)	19.09 lb(US) (8.66 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	10.59 in (26.9 cm)
Package 1 width	13.19 in (33.5 cm)
Package 1 Length	18.39 in (46.7 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------