

LC1DMKG7

Capacitor contactor, TeSys Deca, 25 kVAR at
400 V/50 Hz, coil 120 V AC 50/60 Hz





Main

Range	TeSys TeSys Deca
Product name	TeSys LC1D.K TeSys Deca
Product or Component Type	Capacitor duty contactor
Device short name	LC1DMK
Device Application	Control
Contactor application	Power factor correction
Utilisation category	AC-6b
Poles description	3P
Power pole contact composition	3 NO
Device location in system	Inside delta interruption Line interruption
[Ue] rated operational voltage	Power circuit 690 V AC 50/60 Hz
Reactive power rating	14 Kvar 230 V AC 50 Hz 140 °F (60 °C) 25 Kvar 400 V AC 50 Hz 140 °F (60 °C) 27 Kvar 440 V AC 50 Hz 140 °F (60 °C) 42 kvar 690 V AC 50 Hz 140 °F (60 °C)
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	120 V AC 50/60 Hz
Auxiliary contact composition	1 NO + 2 NC instantaneous
Electrical durability	300000 Cycles 400 V 200000 cycles 690 V
Mounting Support	DIN rail Plate
Standards	EN/IEC 60947-1 EN/IEC 60947-4-1 IEC 60335-1
Product Certifications	IECEE CB Scheme UKCA
Connections - terminals	Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²) solid Control circuit screw clamp terminals 2 0.00... 0.01 in ² (1...4 mm ²) solid Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²) flexible without cable end Control circuit screw clamp terminals 2 0.00... 0.01 in ² (1...4 mm ²) flexible without cable end Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²) flexible with cable end Control circuit screw clamp terminals 2 0.00... 0.00 in ² (1...2.5 mm ²) flexible with cable end Power circuit screw clamp terminals 1 0.00...0.02 in ² (2.5...16 mm ²) solid Power circuit screw clamp terminals 2 0.00...0.01 in ² (2.5...6 mm ²) solid Power circuit screw clamp terminals 1 0.00...0.02 in ² (1.5...10 mm ²) flexible without cable end Power circuit screw clamp terminals 2 0.00...0.01 in ² (1.5...6 mm ²) flexible without cable end Power circuit screw clamp terminals 1 0.00...0.02 in ² (1...10 mm ²) flexible with cable end Power circuit screw clamp terminals 2 0.00...0.01 in ² (1...4 mm ²) flexible with cable end
Tightening torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 22.13 lbf.in (2.5 N.m) screw clamp terminals
Maximum operating rate	240 cyc/h

Complementary

Auxiliary contacts type	Mechanically linked 1 NO + 2 NC IEC 60947-5-1
-------------------------	---

Environment

IP degree of protection	IP20 front face IEC 60529
Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Operating altitude	0...9842.52 ft (0...3000 m)
Height	4.92 in (125 mm)
Width	1.77 in (45 mm)
Depth	5.00 in (127 mm)
Net Weight	1.39 lb(US) (0.63 kg)

Ordering and shipping details

Category	22354-CTR, TESYS D, OPEN, 9-38A AC
Discount Schedule	I12
GTIN	3606480401589
Nbr. of units in pkg.	1
Package weight(Lbs)	21.69 oz (615.0 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.76 in (7 cm)
Package 1 width	7.87 in (20 cm)
Package 1 Length	9.06 in (23 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------