



Overview

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

Main

Main Input Voltage	3 phase
Main Output Voltage	120 V 208 V 3 phase
Number of rack unit	0U
Number of cables	1
Provided Equipment	Installation guide User Manual

Physical

Color	Black
Height	80.98 in (205.7 cm)
Width	24.02 in (61 cm)
Depth	35.98 in (91.4 cm)
Net Weight	1058.22 lb(US) (480 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	60 Hz +/- 3 Hz
-----------------	----------------

Output

Maximum Total Current Draw per Phase	139 A
Efficiency	98 %

Conformance

Product Certifications	CUL Listed
Standards	UL 60950

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	32...113 °F (0...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...30000 ft (0.00...9144.00 m)

Ordering and shipping details

GTIN	731304221036
Package weight(Lbs)	1080.27 lb(US) (490 kg)

Packing Units

Package 1 Height	85.98 in (218.4 cm)
Package 1 width	35.98 in (91.4 cm)
Package 1 Length	47.99 in (121.9 cm)
Number of Units in Package 3	1

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------