



Overview

Lead time	Usually in Stock
-----------	------------------



Main

Main Input Voltage	208 V
Number of rack unit	3U
Number of cables	1.0
Battery Type	Lead-Acid battery
Provided Equipment	Installation guide Rack Mounting brackets User Manual

Physical

Color	Black
Height	5.12 in (13 cm)
Width	17.01 in (43.2 cm)
Depth	25.98 in (66 cm)
Net Weight	200.42 lb(US) (90.91 kg)
Mounting Mode	Rack-mounted
USB compatible	No

Conformance

Standards	OSHDP
-----------	-------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Storage Relative Humidity	0...95 % non-condensing

Batteries & Runtime

Battery blocks per string	16
Battery Slots Empty	0
Included Battery Modules	4
Battery manufacturer	Panasonic
Device mounting	Stand alone battery stack
Battery Voltage	192V
Additional information	Replace all batteries in operation together (UPS internal and external batteries) all-at-once
RBC Quantity	2

Ordering and shipping details

GTIN	731304259336
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.26 in (41.3 cm)
Package 1 Width	39.37 in (100 cm)
Package 1 Length	23.62 in (60 cm)
Package 1 Weight	223.46 lb(US) (101.36 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace, optional on-site warranties available, optional extended warranties available
----------	--