

Product data sheet

Specifications



license, Ecostruxure Machine Expert, addon, Asi safety, node locked, single, 1 user

ESESADCZZSPAZZ

Main

Range of product	EcoStruxure Machine Expert
Product or component type	License
Format	Digital
Software type	Add-on
Type of license	Node locked license
Variant	ASi safety
Software version	V2.2
Operating system requirement	Windows 10 32/64 bit Windows 11 32/64 bit
User language	English Spanish Chinese French German Italian Portuguese (Brazilian) Turkish Japanese

Complementary

License category	Permanent
Software function	Engineering Programming safety PLC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Range compatibility	Modicon M241 Modicon M251 Modicon M262 Modicon TM3 Modicon TM5 Modicon TM7 PacDrive LMC Eco PacDrive LMC Pro PacDrive LMC Pro2 Preventa XPSMC Preventa XPSMCM Lexium 32 Lexium 32i Lexium 32M Lexium 52 Lexium 62 Lexium ILA Lexium ILE Lexium ILS Lexium SD3 Altivar 320 Altivar 340 Altivar Process ATV600 Altivar Easy 610 Altivar 660 Drive System Altivar Process ATV900 Altivar Process 980 Regenerative Drive System Harmony XB5R Harmony XB4R OsiSense XG OsiSense XUW TeSys U TeSys T TeSys island Magelis XBT GH Magelis GTO Magelis GTU Magelis GTUX Magelis iPC Magelis STO & STU Magelis GK Magelis SCU EcoStruxure Machine Expert Twin
Communication port protocol	Modbus SL Modbus TCP EtherNet/IP CANopen Sercos III CANmotion
Hosting option	On-premise
License size	Single (1 user)
System requirements	8 GB RAM 15 GB hard disk space
Processor requirement	Intel Core 2 Duo
Display resolution	1280 x 1024 pixels

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 g