



### Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

### Main

|                     |                    |
|---------------------|--------------------|
| Number of rack unit | 44U                |
| Provided equipment  | Installation guide |

### Physical

|                            |                                |
|----------------------------|--------------------------------|
| Color                      | Black                          |
| Height                     | 83.86 in (213 cm)              |
| Width                      | 23.62 in (60 cm)               |
| Depth                      | 29.41 in (74.7 cm)             |
| Net Weight                 | 92.20 lb(US) (41.82 kg)        |
| Mounting preference        | No preference                  |
| Mounting Mode              | Not rack-mountable             |
| Maximum Mounting Depth     | 29.13 in (73.99 cm)            |
| Minimum Mounting Depth     | 29.13 in (73.99 cm)            |
| Rack width                 | 19"                            |
| Permanent permissible load | 2000 lb(US) (907.18 kg) static |

### Conformance

|           |          |
|-----------|----------|
| Standards | EIA-310E |
|-----------|----------|

### Ordering and shipping details

|      |              |
|------|--------------|
| GTIN | 731304260264 |
|------|--------------|

### Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type of Package 1       | PCE                      |
| Number of Units in Package 1 | 1                        |
| Package 1 Height             | 82.01 in (208.3 cm)      |
| Package 1 Width              | 7.40 in (18.8 cm)        |
| Package 1 Length             | 10.00 in (25.4 cm)       |
| Package 1 Weight             | 102.21 lb(US) (46.36 kg) |

## Offer Sustainability

|                            |                                                                                                                                                                                    |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                              |
| REACH Regulation           |  <a href="#">REACH Declaration</a>                                                                |
| REACH free of SVHC         | Yes                                                                                                                                                                                |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes                                                                                                                                                                                |
| Mercury free               | Yes                                                                                                                                                                                |
| RoHS exemption information |  <a href="#">Yes</a>                                                                              |
| Take-back                  | Take-back program available                                                                                                                                                        |

## Contractual warranty

|          |                          |
|----------|--------------------------|
| Warranty | 5 year repair or replace |
|----------|--------------------------|