

Product data sheet

Characteristics

DZ5CE005L6D

INSULATE CABLE END 0,5ODI



Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Linergy
Product or component type	Cable end
Cable end size	Short
Standards	DIN 46228-4
Type of packing	String of bags
Quantity per set	10 sets of 100
Cable cross section	0 in ² (0.5 mm ²)

Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Color	White
Bezel material	Halogen-free plastic
Tube material	Copper conforming to ISO 1337
Number of cables	1
AWG gauge	AWG 22
Bezel size	Ø 3.1 mm
Tube diameter	0.05 in (1.3 mm)
Length	0.47 in (12 mm)
Tube length	6 mm
Product weight	0.19 lb(US) (0.085 kg)

Environment

Product certifications	UL
Ambient air temperature for operation	-4...221 °F (-20...105 °C)

Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discount Schedule	I
GTIN	00785901950141
Nbr. of units in pkg.	1000
Package weight(Lbs)	0.01
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0437 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------
