



PART NO.	'L' DIM.
1439-1	.062 [1.57]
1439-2	.094 [2.39]
1439-3	.125 [3.18]
1439-4	.156 [3.96]

NOTES:

1. BODY: MAT'L - BRASS
SPRING CONTACT: MAT'L - BERYLLIUM COPPER
2. MOUNTING HOLE DIA.: .067 [1.70]

TOLERANCE ON DIAMETERS: $\pm .002$

KEYSTONE ELECTRONICS CORP.

www.keyelco.com • NEW HYDE PARK NY 11040 • Tel (516)328-7500

PART NAME

MICRO JACK, SWAGE MOUNT

MATERIAL

AS NOTED

FINISH TIN/LEAD PLATE	DRN BY BOONE	DATE 2.05.07
	APP'D RH	SCALE 5X
TOLERANCES DECIMAL $\pm .005$ [± 0.13] ANGULAR $\pm 1^\circ$ UNLESS OTHERWISE SPECIFIED	CODE C	DWG NO. 1439-1 -1439-4
DATE	DESCRIPTION	REV.