





THIS DOCUMENT IS THE PROPERTY OF  
KEYSTONE ELECTRONICS CORP. AND  
SHALL NOT BE REPRODUCED, DISTRIBUTED  
OR USED AS A BASIS FOR MANUFACTURE  
WITHOUT PRIOR WRITTEN PERMISSION  
FROM KEYSTONE ELECTRONICS CORP.

# MTG. DETAIL



## ACTUAL SIZE



## SECTION A-A

.059 [1.50] (E1)

|          |                                             |      |
|----------|---------------------------------------------|------|
| 6.29.23  | ADD MTG LEG (E1)<br>CHANGE AS PER ECN23-110 | E    |
| 12.14.22 | CHANGE AS PER ECN22.178                     | D    |
| 10.11.22 | CHANGE AS PER ECN22-155                     | C    |
| 10.03.22 | CHANGE AS PER ECN22-155                     | B    |
| 7.12.22  | CHANGE AS PER ECN 22-128                    | A    |
| DATE     | DESCRIPTION                                 | REV. |

| KEYSTONE ELECTRONICS CORP.                                   |                 |                         |         |
|--------------------------------------------------------------|-----------------|-------------------------|---------|
| www.keyelco.com • NEW HYDE PARK NY 11040 • Tel (516)328-7500 |                 |                         |         |
| PART NAME                                                    |                 | THM MAXI FUSE CLIP      |         |
| MATERIAL                                                     |                 | .016 [0.41] TH'K COPPER |         |
| FINISH                                                       |                 | DRN BY                  | NT      |
| TIN NICKEL PLATE                                             |                 | DATE                    | 4.01.22 |
|                                                              |                 | APP'D                   | MR      |
|                                                              |                 | SCALE                   | 4X      |
| TOLERANCES                                                   | INCH [MM]       | CODE                    | DWG NO. |
| DECIMAL                                                      | ± .005 [± 0.13] | C                       |         |
| ANGULAR                                                      | ± 1°            |                         |         |
| UNLESS OTHERWISE SPECIFIED                                   |                 |                         |         |

3581-1