

Sales Outline Drawing

May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.

Specifications:

Panel Hole	16 mm
Rated Current, Voltage	5A, 36 VDC / 5A, 250 VAC
Contact Resistance	≤50mΩ
Insulation/Voltage Resistance	1800V
Isolation Resistance	≥1000MΩ
Circuit	1NO1NC SPDT
Operating Temperature	-25 °C to 65 °C
Ingress Protection Rating	IP65 IK09
Mechanical Life	≥500000
Material, Button	304 SS / 6063 aluminum alloy
Material, Shell Sleeve	H59 Brass / 304 SS / 6063 aluminum alloy
Material, Button Pin	H62 Brass
Rubber Ring	SIL silica gel
Material, Nut	H59 Brass
Material, Housing	PA66 + GF20% Nylon
Material, Terminal	AgCdO12
Accessories	1 Nut, 1 Gasket

RoHS Compliant

