

Sales Outline Drawing

May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.

Specifications:

Panel Hole	22.3 mm
Rated Current, Voltage	5A/250VAC; 10A/110VAC
Contact Resistance	≤50mΩ
Insulation Resistance	≥2MΩ
Switch Operation Stroke	5±0.5mm
Circuit	1NO + 1NC
Operating Temperature	-20 °C to 70 °C
Ingress Protection Rating	IP65
Mechanical Life	≥100000
Material, Housing/Base	PA66
Material, Terminal	Nickel-plated brass
Material, Button	PC
Material, Nuts	PA66 M22*1
Operation Type	Self-Locking, SPDT
LED Color	Red, Green, Blue, Yellow, White
LED Voltage	6, 12, 24, 110, 220, 380 Vac/dc
LED Life typ.	40,000 hours

RoHS Compliant

