

## Sales Outline Drawing

Revision

D

**May not be suitable for all medical and aerospace applications.**

**Specifications: Contact Mallory Sonalert to discuss your application.**

Resonant Frequency (Hz)	4000 $\pm$ 500
Operating Voltage (Vp-p/max)	30
Rated Voltage (Vp-p)	3.0
Current Consumption (mA/max)	1.5 at Rated Voltage
Sound Pressure Level (dB/min)	80 at 10cm at Rated voltage
Capacitance (pF)	15,000 $\pm$ 30% at 120Hz
Operating Temperature (°C)	-20 ~ +60
Storage Temperature (°C)	-30 ~ +70
Housing	PPO plastic resin (Color: Black)
Lead Pins	Tin Plated Brass
Weight (Grams)	0.8
Condition by wave soldering (°C)	260 $\pm$ 5 / within 5 sec
Condition by hand soldering (°C)	350 $\pm$ 20 / within 5 sec
Options	For other options contact factory

## NO CIRCUITRY

**Dimensions:** (units: mm)

**ROHS Compliant**

