

Sales Outline Drawing

Revision

F

**May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.**

NO CIRCUITRY

| | |
|----------------------------------|---|
| Resonant Frequency (Hz) | 2000 \pm 500 |
| Operating Voltage (Vp-p/max) | 25 |
| Rated Voltage (Vp-p) | 3.0 |
| Current Consumption (mA/max) | 1.5 at Rated Voltage |
| Sound Pressure Level (dB/min) | 72 at 10cm at Rated voltage typical |
| Capacitance (pF) | 14,000 \pm 30% at 120Hz |
| Operating Temperature (°C) | -20 ~ +100 |
| Storage Temperature (°C) | -30 ~ +110 |
| Housing | PBT1200 UL94HB plastic resin (Color: Black) |
| Lead Pins | Tin Plated Brass |
| Weight (Grams) | 1.6 |
| Condition by wave soldering (°C) | 260 \pm 5 / within 5 sec |
| Condition by hand soldering (°C) | 350 \pm 20 / within 5 sec |
| Options | For other options contact factory |

Dimensions: (units: mm)**ROHS Compliant**